


SPECIFICATIONS STAINLESS STEEL GLASS OVER WIRE STALL FRONTS



Options:

- Available with or without Thresholds
- Available with or without Dog Bowl Inserts in the door
- Available with FRP or WilsonArt Privacy Panel
- Gate hinges can be located on right or left side
- Fixed portion of stall front can be located on right or left side



*Stall Fronts are measured by Run Width and are available in one-inch increments from 43 to 72 inches wide.

NOTE:

All dimensions
are $\pm 1/8$ "